

Next Level in Radiation Detection

- Industry leading technology
- Fast reacting alarm response with isotopic identification
- Utilizes gamma spectra energy deconvolution technique
- State of the art large volume, high resolution Thallium Doped Sodium Iodide crystal (NaI(Tl)) scintillation detectors
- Standalone technology or combined with PVT based systems
- Flexible installation allowing for use in a variety of applications and industrial settings
- Stabilization without a radioactive check source
- Neutron detection capability (Optional)

RC7000

NEUSPEC SPECTROSCOPIC RADIATION DETECTION SYSTEMS

Next Level in Radiation Detection

The RC7000 utilizes gamma spectra energy deconvolution techniques, a significant improvement over conventional PVT scintillator based systems. This technology is specifically designed to enhance a radiation detection systems ability to recognize specific Gamma energies which can adversely affect alarm thresholds. The RC7000 utilizes a series of advanced isotopic identification algorithms in conjunction with RadComm's industry-leading and proven Region Of Interest (R.O.I.) analyses to provide best in class detection and identification.

Stabilization Without a Radioactive Check Source

RC7000 systems incorporate large sodium iodide thallium doped crystals (NaI(Tl)) specifically selected for high resolution signal response. The crystals are protected inside a stainless steel case with a low density aluminum door. To ensure the best possible spectral analyses, the sodium iodide crystals must be continuously stabilized. The RC7000 stabilizes these crystals with specific Gamma energies associated with the ambient background energies, thus eliminating the need for a radioactive check source.

Flexible Multiple Applications

The RC7000 can be used in a variety of applications including: enhancement of an existing PVT based vehicle monitoring system, conveyor belt and area monitoring. RC7000's gamma spectra energy deconvolution algorithms give the system the ability to either ignore (for example NORM or medical isotopes) or alarm on specific gamma energies.



RC7000 Series Components

- Detector assemblies
- RadLink embedded controller
- Smart Infrared presence sensors
- Large touchscreen monitor
- Remote communications package (Optional)

RadLink Controller Features

- Large touchscreen LCD monitor
- Large storage capacity for system operational information and alarms
- Easy to follow multilingual menu outlines and descriptions
- Multi-level security password control
- Detailed alarm and scan data storage
- Easy to set alarm configuration menu
- Network access for remote service and monitoring
- Radiation levels displaying in either: CPS, R/h, Sv/h
- Vehicle speed measurement in Km/h or mph
- Internal operating temperature displayed in Celsius & Fahrenheit
- Adjustable audio alarm
- Counter for number of scans in a 24 hour period for incoming and outgoing scans
- Detailed alarm information displayed and stored after every alarm
- Configurable email reporting
- Various string outputs available

Detector Features


- Detector case: 36"H(915cm)x 24"L(60cm)x 6"W(15cm)
- Outer detector case: painted aluminum
- NEMA 4 (IP65) rated
- Integral PMTs with EM shielding
- High speed DSP circuitry with High SNR
- Ultra stable high voltage software adjustable
- Temperature sensor
- Internal operating temperature: -20°C (-4°F) +55°C (131°F)
- Relative humidity: 93% non-condensing at 40°C (104°F)
- Vibration: 2 g for 15 min at 10 – 33 Hz in XYZ directions (ANSI N42.34, ANSI N42.38)
- Shock: Complies with ANSI N42.34, ANSI N42.38
- EM compatibility: ANSI N42.34, ANSI 42.38 compliant
- CE compliant (EU safety, RFI and EMI directives)

Spectrometer Specifications


- NaI(Tl) Crystal - Variety of sizes available
- Energy Resolution 8.0% or better for 662 KeV
- Energy Range: 20 KeV to 3.0 MeV (Gamma)
- System Calibration Software Monitor with Operator Alert
- Dose Rate Range 1nSv/h to 1.0mSv/h Auto-Ranging
- Gamma Spectrum - 512 Channels, channel capacity 16 bits
- Correction - non-linear energy calibration
- Detection Specification: Meets ANSI N42.38 (2006)

Options


- Camera
- External alarms
- Supervisory software
- Neutron detection (He3 or alternative)




Cobalt-60 Spectra



Thorium-232 Spectra



Cesium-137 Spectra



Barium-133 Spectra



Corporate Head Office

Scott Aikin
Saikin@radcommsystems.com
Jeff Adams
jadams@radcommsystems.com
2931 Portland Drive
Oakville, ON Canada L6H 5S4
Tel. +1 (905) 829-8290
Toll Free. 1 (800) 588-5229
Fax. +1 (905) 829-1406

USA

Joshua Hunter
jhunter@radcommsystems.com
602 E. Lincolnway Ave.
Valparaiso, IN USA 46383
Tel. +1 (773) 680-8430
Toll Free. 1 (800) 588-5229
Fax. +1 (219) 510-5764

Europe

Wim van Hove
wim.van.hove@radcommmeurope.com
Watertorenweg 32, 2230 Herselt, Belgium
Tel. +32.14.75.02.13
Fax. +32.14.75.02.16

China

Zhenhau Wang
wang.zhenhau@ehc-global.com
212-215 Malu Industrial Park, No. 58
Chen Bao Rd., Jiading
Shanghai, 201801, China
Tel. +86-21-69153031
Fax. +86-21-69153231

Latin America

Eduardo Ballesteros
analiticacontrol@prodginy.net.mx
Amatista No.27, El Pedregal
Atizapan de Zaragoza, 52948, Estado De Mexico
Tel. (52) 55 5077 4633/ (52) 55 3615 4910

Black Sea

Osman Tureyyen
metkim@metkim.com
Kavacik, Onarimli Sokak
No 9 Altay Han
Daire: 8 Beykoz, Istanbul, Turkey
Tel. +90 (216) 425-1412
Fax. +90 (216) 425-1432

India

Neelakshi Bhargava
neelakshi@radcommsystems.co.in
C-34, Ground Floor, Sawan Park, Ashok Vihar
New Delhi 110052, India
Tel. +91-9717671924
Fax. +91-9818650118